

36152010

Switch-discon-fuse FUSERBLOC-Dir R OP-100A-2P-NFC-Fuse 22x58

Strong points

- Improved safety
- High breaking capacity
- Specific functionalities for simplified use

General characteristics

- 25 to 400 A.
- Up to 690 VAC.
- Up to 100 kA.
- Available in 2P, 3P or 4P from 25 to 400.

Compliance with standards

- IEC 60947-3
- IEC 60269-1
- IEC 60269-2

Link to the reference

<https://apac.socomec.com/en/reference/36152010>

FUSERBLOC are manually operated multipolar fuse combination switches. They make and break on load and provide safety isolation and protection against overcurrent for any low voltage electrical circuit.

Classification

UNSPSC	39122233
ETIM Class	EC001040
IGCC	5291

Commerce

Effective date	1991-06-03
Obsolescence date	2023-12-30
Production ban date	2024-03-30
Country of origin	TN
Length of the product unit	0.162
Width of the product unit	0.15
Depth of the product unit	0.173
Weight	1.3

ETIM - Electrical characteristics

Max. rated operation voltage Ue AC [V]	690
Rated permanent current Iu [A]	100
Rated operation power at AC-23, 400 V [kW]	51
Conditioned rated short-circuit current Iq [kA]	100
Number of poles	2

ETIM - Mechanical characteristics

Cable entry	Top/bottom
Equipped with connectors	No
Suitable for floor mounting	Yes
Suitable for front mounting	Yes
Suitable for busbar mounting	No
Degree of protection (IP), front side	IP20

ETIM - Technical features

Version as main switch	Yes
Version as safety switch	Yes
Suitable for fuses	22x58 mm
With error protection	No
Type of electrical connection of main circuit	Bolt connection
Type of control element	Rocker lever
Position control element	Right
Motor drive optional	No
Motor drive integrated	No
Version as emergency stop installation	Yes

Logistics

GTIN/EAN	3596031174867
Customs number	8536303099
Price unit	PC
Weight of the packing unit	1.3
Length of the packing unit	0.05
Width of the packing unit	0.16

Depth of the packing unit	0.17
Norms	
Conformity to standards	IEC
Technical Characteristics	
Fuse size	22x58
Number of poles	2
Rated current	100
Type	I-0
Frame size	3