

36253024

Switch-discon-fuse FUSERBLOC W/O handle-L R OP-250A-3P-BS-Fuse B1-B3

Strong points

- Improved safety
- High breaking capacity
- Multi-use
- Simplified use

General characteristics

- For industrial fuses up to 1250 A.
- 2P, 3P or 4P available.
- Up to 690 VAC.
- Up to 100 kA.

Compliance with standards

- IEC 60947-3
- BS EN 60947-3
- IEC 60269-1
- IEC 60269-2

Link to the reference

<https://apac.socomec.com/en/reference/36253024>

FUSERBLOC BS 88 units with right front-side operation are manually-operated multipole fuse load break switches. They provide make and break on load and safety isolation and protection against overcurrent for any low voltage electrical circuit. This range is available in direct and external operation, in 2, 3 and 4 poles and up to 1250 A.

----- System -----

Fill rate E-Order Common	83
Fill rate E-Order Selection	80

Classification

UNSPSC	39122233
ETIM Class	EC001040
IGCC	5291

Commerce

Effective date	1992-09-29
Obsolescence date	2023-06-30
Production ban date	2023-12-30
Country of origin	FR
Discount Policy	1CC44
Discount Policy Label	FUSERBLOC MODUL BS
Length of the product unit	0.195
Width of the product unit	0.253
Depth of the product unit	0.173
Weight	3.55

ETIM - Electrical characteristics

Max. rated operation voltage Ue AC [V]	690
Rated permanent current Iu [A]	250
Rated operation power at AC-23, 400 V [kW]	63
Conditioned rated short-circuit current Iq [kA]	100
Number of poles	3

ETIM - Mechanical characteristics

Cable entry	Top/bottom
Equipped with connectors	No
Suitable for floor mounting	Yes
Suitable for front mounting	Yes
Suitable for busbar mounting	No
Degree of protection (IP), front side	IP20

ETIM - Technical features

Version as main switch	Yes
Version as safety switch	Yes
Suitable for fuses	Shape B1-B3
With error protection	No
Type of electrical connection of main circuit	Bolt connection
Type of control element	Rocker lever
Position control element	Right
Motor drive optional	No

Motor drive integrated	No
Version as emergency stop installation	Yes
Logistics	
GTIN/EAN	3596031179411
Customs number	8536309090
Price unit	PC
Weight of the packing unit	3.55
Length of the packing unit	0.17
Width of the packing unit	0.17
Depth of the packing unit	0.26
Norms	
Conformity to standards	IEC
Technical Characteristics	
Fuse size	B1-B3
Number of poles	3
Rated current	250
Type	I-0
Frame size	5