

38U13050

Switch-discon-fuse FUSERBLOC Ur-Ext&Dir F/L R OP-500A-3P-uR-Fuse 2 - K110

Strong points

- Limiting the short-circuit current
- Optimum safety
- High breaking capacity

General characteristics

- For high-speed fuses up to 1250 A.
- Up to 690 VAC in AC22B and 1250 VDC in DC20.
- Cylindrical, knife type, K50 and K110 uR fuses up to 1250 VDC off load.

Compliance with standards

- IEC 60947-3
- EN 60947-3

Link to the reference

FUSERBLOC uR are multipole fuse combination switches with manual right and front operating and high-speed fuses.

When used in combination with high-speed fuses (uR curve), they can break or make under load, provide safe isolation and protection from overcurrent for power semiconductors (variable drives, inverters, etc.) up to 1250 A.

This range includes versions for direct and external operation, 2, 3 and 4 poles and up to 1250 A.

----- System -----

Fill rate E-Order Common	14
Fill rate E-Order Selection	83
Classification	
UNSPSC	39122233
ETIM Class	EC001040
IGCC	5291
Commerce	
Effective date	2004-02-04
Country of origin	FR
Discount Policy	1CC35
Discount Policy Label	FUSER MOD. DIN >400
ETIM - Electrical characteristics	
Max. rated operation voltage Ue AC [V]	690
Rated permanent current Iu [A]	500
Number of poles	3
ETIM - Mechanical characteristics	
Cable entry	Top/bottom
Equipped with connectors	No
Suitable for floor mounting	Yes
Suitable for front mounting	Yes
Suitable for busbar mounting	No
Degree of protection (IP), front side	IP20
ETIM - Technical features	
Version as main switch	Yes
Version as safety switch	Yes
Suitable for fuses	NH2
With error protection	No
Type of electrical connection of main circuit	Bolt connection
Type of control element	Long turning handle
Position control element	Front side
Motor drive optional	No
Motor drive integrated	No
Version as emergency stop installation	Yes
Logistics	
GTIN/EAN	3596031729692
Customs number	8536309090
Price unit	PC
Weight of the packing unit	6

<https://apac.socomec.com/en/reference/38U13050>

Norms

Conformity to standards	IEC
-------------------------	-----

Technical Characteristics

Control operator	Direct : H1 / External : S3
Fuse size	NH2 - K110
Number of poles	3
Rated current	500
Type	I-0
Frame size	17