

**48290110**

## Current module DIRIS Digiware I-30, 3 current inputs, Metering



### Strong points

- Multi-circuit
- Accurate
- Compact
- Plug & Play
- Leading edge technology
- MID certified and more

### General characteristics

- Versions with 3, 4 or 6 RJ12 current inputs.
- Compatible with TE, TR/iTR and TF current sensors.
- DIN rail assembly.

### Compliance with standards

- IEC 61557-12
- UL 61010 Guide PICQ File E257746
- ANSI C12.20
- EN 50470-1
- EN 50770-3
- Directive 2014/32/EU

### Link to the reference

<https://apac.socomec.com/en/reference/48290110>

DIRIS Digiware Iac modules measure consumption and monitor the installation as close as possible to loads. Their flexibility allows you to distribute the loads to meter or monitor independent current inputs (for example: 1 three-phase load or 3 single-phase loads).

<b>Classification</b>	
UNSPSC	83101808
ETIM Class	EC002301
IGCC	6042
<b>Commerce</b>	
Effective date	2013-11-22
Country of origin	FR
<b>ETIM - Electrical characteristics</b>	
Sampling frequency [Hz]	10000
Number of current measurement inputs	3
Voltage type (supply voltage)	DC
Supply voltage DC [V]	0.24..0.24
Supporting protocol for IEC 61850 Ethernet	No
Supporting protocol for OPC UA PubSub	No
Supporting protocol for PROFIBUS	No
Supporting protocol for Modbus	Yes
Supporting protocol for PROFINET IO	No
Supporting protocol for other bus systems	No
With audit logging (audit log)	No
With firmware signature	Yes
With logging of security events (security event log)	Yes
With Role Based Access Control (RBAC)	No
Web server with HTTPS transfer protocol	No
<b>ETIM - Mechanical characteristics</b>	
Width [mm]	18
Height [mm]	90
Depth [mm]	65
Degree of protection (IP), front side	IP20
<b>ETIM - Technical features</b>	
Ampere meter	Yes
Blind power meter	Yes
With rotational speed meter	No
Frequency meter	No
Pulse counter	No
Voltmeter	No
Effective power measurement device	Yes
Remote display	No
<b>Logistics</b>	
GTIN/EAN	3596032776381
Customs number	9030337000
Price unit	PC
Weight of the packing unit	0.09
Length of the packing unit	0.115

Width of the packing unit	0.08
Depth of the packing unit	0.03
<b>Norms</b>	
Conformity to standards	IEC UL
<b>Technical Characteristics</b>	
Application	Metering
Model	I-30
Number of current inputs	3
Type	Current acquisition module