

48290502

Solid current sensor TE-25 25mm 40-160A



Strong points

- Plug & Play
- Accuracy as per standard IEC 61557-12
- Installation

General characteristics

- Range from 5 to 2000A.
- used with DIRIS Digiware, DIRIS A-40 and DIRIS B.

Compliance with standards

- IEC 61557-12
- ISO 14025
- UL

Link to the reference

<https://apac.socomec.com/en/reference/48290502>

TE smart current sensors measure the load currents of an electrical system and send the data to meters and measurement hubs via an RJ12 plug-and-play output. Thanks to a wide measurement range, TE current sensors cover the full current range of 5 to 2000 A, with 7 references. TE solid current sensors can be connected to DIRIS Digiware, DIRIS A-40 and DIRIS B via a rapid RJ12 connection. Numerous accessories are available to aid the installation of sensors in any type of cabinet.

===== System =====

Fill rate E-Order Common	29
Fill rate E-Order Selection	100

Classification

UNSPSC	83101808
ETIM Class	EC002048
IGCC	6042

Commerce

Effective date	2013-11-22
Country of origin	FR
Discount Policy	1EN30
Discount Policy Label	SENSORS

ETIM - Electrical characteristics

Rated primary current [A]	160
Rated secondary current [A]	0.1
Rated secondary apparent power [VA]	0.1
Accuracy class	0.2S
Overcurrent limiting factor	FS 10
Calibrated	Yes

ETIM - Mechanical characteristics

With contact protection	Yes
Height opening [mm]	13.5..13.5
Width opening [mm]	13.5..13.5
Opening diameter [mm]	13.5
Snap mounting	Yes
With copper rail	Yes
Secondary connection	Plug-in connection

ETIM - Technical features

Model	Through-feed current converter
Number of primary inputs	1

Logistics

GTIN/EAN	3596032776480
Customs number	8504312990
Price unit	PC
Weight of the packing unit	0.08
Length of the packing unit	0.07
Width of the packing unit	0.033
Depth of the packing unit	0.025

Norms

Conformity to standards	IEC UL
-------------------------	------------

Technical Characteristics

Model	TE
Opening	13.5x13.5
Rated current	160
Secondary rated current	RJ12