

48290573

## TF-40 100-400A ROGOWSKI SENSOR RJ12



TF flexible current sensors measure the load currents of an electrical circuit and send the data to meters and Power Monitoring Devices or current modules via an RJ12 plug-and-play connection. Thanks to a wide measurement range, TF current sensors cover a wide current range from 100 to 6000 A, with only 7 references. TF flexible current sensors can be used with DIRIS Digiware I modules, DIRIS A-40 and DIRIS B.

### Strong points

- Plug & Play
- Accuracy as per standard IEC 61557-12
- Safe locking mechanism
- Installation
- Simplified installation

### General characteristics

- Range from 150 to 6000A.
- Used with DIRIS Digiware, DIRIS A-40 and DIRIS B.

### Compliance with standards

- IEC 61557-12
- ISO 14025
- UL

### Link to the reference

<https://apac.socomec.com/en/reference/48290573>

### Classification

UNSPSC	83101808
ETIM Class	EC002048
IGCC	6042

### Commerce

Effective date	2019-09-01
Country of origin	IT

### ETIM - Electrical characteristics

Rated primary current [A]	400
Rated secondary current [A]	0.1
Rated secondary apparent power [VA]	0.1
Accuracy class	0.2S
Overcurrent limiting factor	FS 10
Calibrated	Yes

### ETIM - Mechanical characteristics

With contact protection	Yes
Height opening [mm]	40..40
Width opening [mm]	40..40
Opening diameter [mm]	40
Snap mounting	Yes
With copper rail	Yes
Secondary connection	Plug-in connection

### ETIM - Technical features

Model	Attachable current transformer
Number of primary inputs	1

### Logistics

GTIN/EAN	3596033018688
Customs number	8504312990
Price unit	PC
Weight of the packing unit	0.1
Length of the packing unit	0.043
Width of the packing unit	0.207
Depth of the packing unit	0.313

### Norms

Conformity to standards	IEC UL
-------------------------	------------

### Technical Characteristics

Model	TF
Opening	40
Rated current	400
Secondary rated current	RJ12