

49821426
Strong points

- Monobloc design
- Plug-in module
- Remote signalling
- End of service life indicator

General characteristics

- Type 2 surge arrester.
- 2, 3 or 4 poles
- For distribution boards
- In: 20 kA.
- I_{max}: 40 kA.
- Common/differential mode.
- Monobloc base.
- Plug-in module.
- Remote signalling.
- End of service life indicator on front

Compliance with standards

- NF EN 61643-11
- IEC 61643-11

Link to the reference

The SURGYS D40 surge arrester is designed to protect LV distribution circuits and equipment from transient surges. It acts against the surges of industrial movements and those due to lightning.

----- System -----

Fill rate E-Order Selection	50
-----------------------------	----

Classification

UNSPSC	39121620
ETIM Class	EC000941
IGCC	4951

Commerce

Effective date	2012-02-06
Obsolescence date	2021-07-31
Production ban date	2021-12-31
Country of origin	CN
Discount Policy	1CG30
Discount Policy Label	SURGYS SURGE ARREST.

Logistics

GTIN/EAN	3596032657345
Customs number	8535400090
Price unit	PC
Weight of the packing unit	0.2
Length of the packing unit	0.084
Width of the packing unit	0.111
Depth of the packing unit	0.207

Norms

Conformity to standards	IEC
-------------------------	-----

Technical Characteristics

Number of poles	2
Protection type	Type 2
Rated voltage	320 VAC
Size	2 Modules

<https://apac.socomec.com/en/reference/49821426>