

49822511



Strong points

- Monobloc design
- Plug-in module
- Remote signalling
- New 1500 VDC version

General characteristics

- Surge arrester type 2 for PV.
- Range from 500 VDC to 1500 VDC.
- MC or MC/MD modes.
- In: 15kA / Imax: 40kA.
- Plug-in.
- Remote signalling (optional).

Compliance with standards

- Compliant with test guides UTE C61-740-51 and NF EN 50 539-11
- Compliant with installation guide UTE C15-712-1 (2010)

Link to the reference

<https://apac.socomec.com/en/reference/49822511>

The SURGYS G51-PV surge arrester is designed to ensure protection for photovoltaic power supply networks against transient surges owing to lightning. It is compliant with the test requirements of UTE C 61-740-51 and EN 50-539-11 as well as with installation requirements UTE C 15-712-1.

Classification

UNSPSC	39121620
ETIM Class	EC000941
IGCC	4951

Commerce

Effective date	2009-12-16
Country of origin	CN

Logistics

GTIN/EAN	3596031986620
Customs number	8535400090
Price unit	PC
Weight of the packing unit	0.309
Length of the packing unit	0.1
Width of the packing unit	0.075
Depth of the packing unit	0.06

Technical Characteristics

Number of poles	2
Network type	PV
Protection type	Type 2
Rated voltage	800 VDC
Size	3 Modules