

41PV4020
Manually operated transfer switch SIRCOVER PV 4P 200A front operation
Strong points

- Stable positions
- Secured breaking
- Patented safety disconnection

General characteristics

- Range from 200A to 630A.
- Available in 2P, 3P or 4P.
- Direct handle or external handle.

Compliance with standards

- IEC 60947-3

Link to the reference

<https://apac.socomec.com/en/reference/41PV4020>

SIRCOVER PV switches are manual multipolar changeover switches with positive break indication. They ensure source inversion or changeover under load of two photovoltaic installation circuits.

----- System -----

Fill rate E-Order Common	29
Fill rate E-Order Selection	75

Classification

UNSPSC	39122205
ETIM Class	EC000216
IGCC	5177

Commerce

Effective date	2011-02-16
Country of origin	FR
Discount Policy	1CH32
Discount Policy Label	SIRCOVER<=630A
Weight	5.76

ETIM - Electrical characteristics

Max. rated operation voltage Ue AC [V]	1000
Rated operating voltage [V]	600..1000
Rated permanent current Iu [A]	200
Number of poles	4

ETIM - Mechanical characteristics

Suitable for floor mounting	No
Suitable for front mounting 4-hole	No
Suitable for front mounting centre	No
Suitable for distribution board installation	No
Suitable for intermediate mounting	Yes
Colour control element	Black
Degree of protection (IP), front side	IP20

ETIM - Technical features

Version as main switch	Yes
Version as maintenance-/service switch	Yes
Version as safety switch	Yes
Version as emergency stop installation	No
Version as reversing switch	Yes
Number of switches	2
Motor drive optional	No
Motor drive integrated	No
Voltage release optional	No
Device construction	Built-in device fixed built-in technique
Type of control element	Door coupling rotary drive
Interlockable	Yes
Type of electrical connection of main circuit	Bolt connection

Logistics

GTIN/EAN	3596032042615
Customs number	8536508090
Price unit	PC

Weight of the packing unit	5.76
Length of the packing unit	0.381
Width of the packing unit	0.241
Depth of the packing unit	0.238
Norms	
Conformity to standards	IEC
Technical Characteristics	
Control operator	Manual I-0-II
Number of poles	4
Rated current	200
Type	Manual I-0-II
Frame size	B3