

49863020



Strong points

- 1-pair or 2-pair version ("x2" model)
- Plug-in modules.
- End of life signal
- Direct earthing
- Common/differential protection modes.

General characteristics

- Din rail plug-in surge protector.
- 1 or 2-pair
- 12 V.
- Impulse current limit: 5 kA.
- Shield wire protection.
- Plug-out without line cut-off.
- Exclusive technology.
- Complete protection.
- End of life management.
- Easy maintenance.

Compliance with standards

- NF EN 61643-21
- IEC 61643-21

Link to the reference

<https://apac.socomec.com/en/reference/49863020>

SURGYS RS-3 surge arresters are designed for transient surge protection of equipment connected to telecommunications and data transmission networks. These surge arresters must be installed on a symmetrical DIN rail and are available for most transmission lines: line voltage 12 V, throughput up to 10 Mbit/s. These products consist of 1 or 2 pairs with a detachable module for easy maintenance.

----- System -----

Fill rate E-Order Common	33
Fill rate E-Order Selection	75

Classification

UNSPSC	39121620
ETIM Class	EC000941
IGCC	4951

Commerce

Effective date	2012-11-15
Country of origin	CN
Discount Policy	1CG30
Discount Policy Label	SURGYS SURGE ARREST.

Logistics

GTIN/EAN	3596032712082
Customs number	8535400090
Price unit	PC
Weight of the packing unit	0.734
Length of the packing unit	0.11
Width of the packing unit	0.08
Depth of the packing unit	0.02

Norms

Conformity to standards	IEC
-------------------------	-----

Technical Characteristics

Number of poles	1
Network type	Telecom & data
Protection type	Low voltage
Rated voltage	15 V