

57010017

RM cylind. fuse holder without sign. aux. cont. (2 mod)-32A-1P+N-NFC-Fuse 10x38



Strong points

- Improved safety
- High breaking capacity
- Format and specific accessories

General characteristics

- Improved safety.
- High breaking capacity.
- Features and options.

Compliance with standards

- IEC 60269-2,-1
- IEC 60269-1
- IEC 60269-2
- UL E307648

Link to the reference

<https://apac.socomec.com/en/reference/57010017>

RMs are modular fuse disconnect switches for cylindrical fuses. They ensure safe disconnection and protection against surges and short-circuits in any low voltage electrical circuit.

Classification	
UNSPSC	39121624
ETIM Class	EC002705
IGCC	4974
Commerce	
Effective date	2012-06-25
Country of origin	ES
Length of the product unit	0.078
Width of the product unit	0.07
Depth of the product unit	0.058
Weight	0.11
ETIM - Electrical characteristics	
Nominal voltage [V]	690
Number of poles	2
Concurrently switching neutral conductor	Yes
ETIM - Mechanical characteristics	
Built-in depth [mm]	40
Degree of protection (IP)	IP2X
Mounting method	DIN rail
For fuse size	10x38 mm
Width in number of modular spacings	2
ETIM - Technical features	
Lockable	Yes
With optical defect indication	No
Logistics	
GTIN/EAN	3596032686901
Customs number	8536105090
Price unit	PC
Weight of the packing unit	0.12
Length of the packing unit	0.065
Width of the packing unit	0.085
Depth of the packing unit	0.04
Norms	
Conformity to standards	IEC UL
Technical Characteristics	
Fuse melting indicator	No
Fuse size	10x38
Number of poles	1+N
Rated current	32
Size	RM32