

**57020011**

## **RM cylind. fuse holder W/O sign. and W/O sign. aux. cont.-50A-1P-Fuse size 10x38**



### **Strong points**

- Improved safety
- High breaking capacity
- Format and specific accessories

### **General characteristics**

- Improved safety.
- High breaking capacity.
- Features and options.

### **Compliance with standards**

- IEC 60269-2,-1
- IEC 60269-1
- IEC 60269-2
- UL E307648

### **Link to the reference**

<https://apac.socomec.com/en/reference/57020011>

RMS are modular fuse disconnect switches for cylindrical fuses. They provide safety disconnection and protection against overloads and short-circuits in any low voltage electrical circuit.

RMS: Fuse disconnect switches with pre-breaking auxiliary contact that signals that the fuse is present / blown.

Classification	
UNSPSC	39121624
ETIM Class	EC002705
IGCC	4974
Commerce	
Effective date	2011-08-30
Country of origin	ES
Length of the product unit	0.11
Width of the product unit	0.106
Depth of the product unit	0.076
ETIM - Electrical characteristics	
Nominal voltage [V]	690
Number of poles	1
Concurrently switching neutral conductor	No
ETIM - Mechanical characteristics	
Built-in depth [mm]	40
Degree of protection (IP)	IP2X
Mounting method	DIN rail
For fuse size	14x51 mm
Width in number of modular spacings	1
ETIM - Technical features	
Lockable	Yes
With optical defect indication	Yes
Logistics	
GTIN/EAN	3596032619619
Customs number	8536105090
Price unit	PC
Weight of the packing unit	0.02
Length of the packing unit	0.1
Width of the packing unit	0.1
Depth of the packing unit	0.001
Norms	
Conformity to standards	IEC UL
Technical Characteristics	
Fuse melting indicator	Yes
Fuse size	14x51
Number of poles	1
Rated current	50
Size	RM/RMS 50