

48290157

Direct Current module DIRIS Digiware I-35dc, 3 DC current inputs, Analysis



Strong points

- Multi-circuit
- Flexible
- Plug & Play
- Compact

General characteristics

- 3 RJ12 current inputs
- DIN-rail mounted

Compliance with standards

- IEC 61557-12
- UL 61010 Guide FTRZ/PICQ File E257746

Link to the reference

<https://apac.socomec.com/en/reference/48290157>

DIRIS Digiware Idc modules measure consumption and monitor the DC electrical installation. Several Idc modules can be used within the same system, allowing the measurement of a large number of DC circuits. They are associated with DIRIS Digiware Udc voltage measurement modules.

Direct current is measured using external sensors connected by RJ12-Molex cables, available in multiple lengths. These cables are colour coded (brown, orange, white) to easily identify circuits.

The associated DIRIS Digiware D screen and the embedded webserver Webview can display electrical measurements from both DIRIS Digiware AC and DC systems simultaneously.

==== System =====

Fill rate E-Order Common	29
Fill rate E-Order Selection	60
Classification	
UNSPSC	83101808
ETIM Class	EC002301
IGCC	6042
Commerce	
Effective date	2018-02-01
Country of origin	FR
Discount Policy	1EN60
Discount Policy Label	MEASUREMENT SYSTEM PACKAGE
ETIM - Electrical characteristics	
Sampling frequency [Hz]	10000
Number of current measurement inputs	3
Voltage type (supply voltage)	DC
Supply voltage DC [V]	0..24
Supporting protocol for IEC 61850 Ethernet	No
Supporting protocol for OPC UA PubSub	No
Supporting protocol for PROFIBUS	No
Supporting protocol for Modbus	Yes
Supporting protocol for PROFINET IO	No
Supporting protocol for other bus systems	No
With audit logging (audit log)	No
With firmware signature	Yes
With logging of security events (security event log)	Yes
With Role Based Access Control (RBAC)	No
Web server with HTTPS transfer protocol	No
ETIM - Mechanical characteristics	
Width [mm]	18
Height [mm]	90
Depth [mm]	65
Degree of protection (IP), front side	IP20
ETIM - Technical features	
Ampere meter	Yes
Blind power meter	Yes
With rotational speed meter	No

Frequency meter	No
Pulse counter	No
Voltmeter	No
Effective power measurement device	Yes
Remote display	No
Logistics	
GTIN/EAN	3596033002892
Customs number	9030900000
Price unit	PC
Weight of the packing unit	0.09
Length of the packing unit	0.03
Width of the packing unit	0.12
Depth of the packing unit	0.06
Norms	
Conformity to standards	IEC UL
Technical Characteristics	
Application	Analysis
Model	I-35DC
Number of current inputs	3
Type	Current acquisition module