


57035002

RM cylind. fuse holder without sign. aux. cont.-100A-2P-NFC-Fuse 22x58



Strong points

- Improved safety
- High breaking capacity
- Format and specific accessories

General characteristics

- Improved safety.
- High breaking capacity.
- Features and options.

Compliance with standards

- IEC 60269-2,-1
- IEC 60269-1
- IEC 60269-2
- UL E307648

Link to the reference

<https://apac.socomec.com/en/reference/57035002>

RMs are modular fuse disconnect switches for cylindrical fuses. They ensure safe disconnection and protection against surges and short-circuits in any low voltage electrical circuit.

Classification

UNSPSC	39121624
ETIM Class	EC002705
IGCC	4974

Commerce

Effective date	2012-06-25
Country of origin	ES
Length of the product unit	0.1265
Width of the product unit	0.143
Depth of the product unit	0.0765
Weight	0.32

ETIM - Electrical characteristics

Nominal voltage [V]	690
Number of poles	2
Concurrently switching neutral conductor	No

ETIM - Mechanical characteristics

Built-in depth [mm]	49.5
Degree of protection (IP)	IP2X
Mounting method	DIN rail
For fuse size	22x58 mm
Width in number of modular spacings	1

ETIM - Technical features

Lockable	Yes
With optical defect indication	No

Logistics

GTIN/EAN	3596032687076
Customs number	8536109090
Price unit	PC
Weight of the packing unit	0.32
Length of the packing unit	0.125
Width of the packing unit	0.08
Depth of the packing unit	0.075

Norms

Conformity to standards	IEC UL
-------------------------	------------

Technical Characteristics

Fuse melting indicator	no
Fuse size	22x58
Number of poles	2
Rated current	100
Size	RM/RMS 100