


**60120020**

## Cylindrical fuse without striker gG type 10x38 500Vac 20A



Industrial fuses protect installations and people from overcurrents for any low voltage electrical circuit.

### Classification

UNSPSC	39121609
ETIM Class	EC002704
IGCC	4905

### Commerce

Effective date	1988-04-15
Country of origin	ES
Discount Policy	1CF10
Discount Policy Label	CYLINDRICAL FUSE
Length of the product unit	0.038
Width of the product unit	0.0103
Weight	0.02

### ETIM

Model	Ceramic fuse
Size	14x51 mm
Voltage type	AC
Rated current [A]	20
Rated voltage [V]	500
Rated operating frequency [Hz]	50..60
Breaking capacity [kA]	120
Power loss at rated current [W]	2

### Logistics

GTIN/EAN	3596031377152
Customs number	8536105090
Price unit	PC
Weight of the packing unit	0.01
Length of the packing unit	0.01
Width of the packing unit	0.01
Depth of the packing unit	0.04

### Norms

Conformity to standards	IEC
-------------------------	-----

### Technical Characteristics

Fuse melting indicator	without striker
Fuse size	10x38
Rated voltage	500 VAC
Rated current	20
Type	gG

### Strong points

- High-performance
- Increased reliability
- Improved safety

### General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

### Compliance with standards

- IEC 60269-1
- IEC 60269-2

### Link to the reference



<https://apac.socomec.com/en/reference/60120020>