

**60130012**

## Cylindrical fuse without striker aM type 10x38 500Vac 12A



### Strong points

- High-performance
- Increased reliability
- Improved safety

### General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

### Compliance with standards

- IEC 60269-1
- IEC 60269-2

### Link to the reference

<https://apac.socomec.com/en/reference/60130012>

Industrial fuses protect installations and people from overcurrents for any low voltage electrical circuit.

<b>Classification</b>	
UNSPSC	39121609
ETIM Class	EC002704
IGCC	4905
<b>Commerce</b>	
Effective date	1988-04-15
Country of origin	ES
Length of the product unit	0.038
Width of the product unit	0.0103
Weight	0.01
<b>ETIM - Electrical characteristics</b>	
Breaking capacity [kA]	120
Power loss at rated current [W]	1.3
Voltage type	AC
Rated current [A]	12
Rated voltage [V]	500
Utilization category	aM (switchgear protection)
Rated operating frequency [Hz]	50..60
<b>ETIM - Mechanical characteristics</b>	
Size	14x51 mm
<b>ETIM - Technical features</b>	
Model	Ceramic fuse
<b>Logistics</b>	
GTIN/EAN	3596031377282
Customs number	8536105090
Price unit	PC
Weight of the packing unit	0.01
Length of the packing unit	0.005
Width of the packing unit	0.005
Depth of the packing unit	0.04
<b>Norms</b>	
Conformity to standards	IEC
<b>Technical Characteristics</b>	
Fuse melting indicator	without striker
Fuse size	10x38
Rated voltage	500 VAC
Rated current	12
Type	aM