

60220008

Cylindrical fuse without striker gG type 14x51 690Vac 8A



Strong points

- High-performance
- Increased reliability
- Improved safety

General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

Compliance with standards

- IEC 60269-1
- IEC 60269-2

Link to the reference

<https://apac.socomec.com/en/reference/60220008>

Industrial fuses protect installations and people from overcurrents for any low voltage electrical circuit.

Classification	
UNSPSC	39121609
ETIM Class	EC002704
IGCC	4905
Commerce	
Effective date	1988-04-15
Obsolescence date	2021-09-01
Production ban date	2022-02-01
Country of origin	ES
Length of the product unit	0.051
Width of the product unit	0.0143
Weight	0.02
ETIM - Electrical characteristics	
Voltage type	AC
Rated current [A]	8
Rated operating frequency [Hz]	50..60
ETIM - Mechanical characteristics	
Size	14x51 mm
ETIM - Technical features	
Model	Ceramic fuse
Logistics	
GTIN/EAN	3596031377428
Customs number	8536101090
Price unit	PC
Weight of the packing unit	0.02
Length of the packing unit	0.013
Width of the packing unit	0.013
Depth of the packing unit	0.05
Norms	
Conformity to standards	IEC
Technical Characteristics	
Fuse melting indicator	without striker
Fuse size	14x51
Rated voltage	690 VAC
Rated current	8
Type	gG