

**60230010**

**Cylindrical fuse without striker aM type 14x51 690Vac 10A**



#### Strong points

- High-performance
- Increased reliability
- Improved safety

#### General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

#### Compliance with standards

- IEC 60269-1
- IEC 60269-2

#### Link to the reference

<https://apac.socomec.com/en/reference/60230010>

Industrial fuses protect installations and people from overcurrents for any low voltage electrical circuit.

<b>Classification</b>	
UNSPSC	39121609
ETIM Class	EC002704
IGCC	4905
<b>Commerce</b>	
Effective date	1988-04-15
Obsolescence date	2021-09-01
Production ban date	2022-02-01
Country of origin	ES
Length of the product unit	0.051
Width of the product unit	0.0143
Weight	0.02
<b>ETIM - Electrical characteristics</b>	
Voltage type	AC
Rated current [A]	10
Utilization category	aM (switchgear protection)
Rated operating frequency [Hz]	50..60
<b>ETIM - Mechanical characteristics</b>	
Size	14x51 mm
<b>ETIM - Technical features</b>	
Model	Ceramic fuse
<b>Logistics</b>	
GTIN/EAN	3596031377589
Customs number	8536101090
Price unit	PC
Weight of the packing unit	0.02
Length of the packing unit	0.013
Width of the packing unit	0.013
Depth of the packing unit	0.05
<b>Norms</b>	
Conformity to standards	IEC
<b>Technical Characteristics</b>	
Fuse melting indicator	without striker
Fuse size	14x51
Rated voltage	690 VAC
Rated current	10
Type	aM