

**60320040**

## Cylindrical fuse without striker gG type 22x58 690Vac 40A



### Strong points

- High-performance
- Increased reliability
- Improved safety

### General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

### Compliance with standards

- IEC 60269-1
- IEC 60269-2

### Link to the reference

<https://apac.socomec.com/en/reference/60320040>

Industrial fuses protect installations and people from overcurrents for any low voltage electrical circuit.

<b>Classification</b>	
UNSPSC	39121609
ETIM Class	EC002704
IGCC	4905
<b>Commerce</b>	
Effective date	1988-04-15
Country of origin	ES
Length of the product unit	0.058
Width of the product unit	0.0222
Weight	0.055
<b>ETIM - Electrical characteristics</b>	
Voltage type	AC
Rated current [A]	40
Rated operating frequency [Hz]	50..60
<b>ETIM - Mechanical characteristics</b>	
Size	14x51 mm
<b>ETIM - Technical features</b>	
Model	Ceramic fuse
<b>Logistics</b>	
GTIN/EAN	3596031377862
Customs number	8536105090
Price unit	PC
Weight of the packing unit	0.055
Length of the packing unit	0.022
Width of the packing unit	0.022
Depth of the packing unit	0.058
<b>Norms</b>	
Conformity to standards	IEC
<b>Technical Characteristics</b>	
Fuse melting indicator	without striker
Fuse size	22x58
Rated voltage	690 VAC
Rated current	40
Type	gG