

49822531



Strong points

- Monobloc design
- Plug-in module
- Remote signalling
- New 1500 VDC version

General characteristics

- Surge arrester type 2 for PV.
- Range from 500 VDC to 1500 VDC.
- MC or MC/MD modes.
- In: 15kA / I_{max}: 40kA.
- Plug-in.
- Remote signalling (optional).

Compliance with standards

- Compliant with test guides UTE C61-740-51 and NF EN 50 539-11
- Compliant with installation guide UTE C15-712-1 (2010)

Link to the reference

<https://apac.socomec.com/en/reference/49822531>

The SURGYS G51-PV surge arrester is designed to ensure protection for photovoltaic power supply networks against transient surges owing to lightning. It is compliant with the test requirements of UTE C 61-740-51 and EN 50-539-11 as well as with installation requirements UTE C 15-712-1.

----- System -----	
Fill rate E-Order Common	33
Fill rate E-Order Selection	50
Classification	
UNSPSC	39121620
ETIM Class	EC000941
IGCC	4951
Commerce	
Effective date	2009-12-16
Country of origin	CN
Discount Policy	1CG30
Discount Policy Label	SURGYS SURGE ARREST.
Logistics	
GTIN/EAN	3596031986606
Customs number	8535400090
Price unit	PC
Weight of the packing unit	0.26
Length of the packing unit	0.1
Width of the packing unit	0.05
Depth of the packing unit	0.06
Technical Characteristics	
Number of poles	2
Network type	PV
Protection type	Type 2
Rated voltage	600 VDC
Size	2 Modules