

49853170



Strong points

- 1-pair or 2-pair version ("x2" model)
- Plug-in modules.
- End of life signal
- Direct earthing
- Common/differential protection modes.

General characteristics

- DIN rail plug-in surge protector.
- For RTC, ADSL2, VDSL2 networks for analogue telephone lines.
- Modes MC or MC/MD;
- 1 or 2-pair
- Un: 170 V.
- Shield wire protection.
- Without line cut-off.
- Exclusive technology.
- Complete protection.
- End of life management.
- Easy maintenance.

Compliance with standards

- NF EN 61643-21
- IEC 61643-21

Link to the reference

<https://apac.socomec.com/en/reference/49853170>

SURGYS TEL-3 surge arresters are designed for transient surge protection of equipment connected to telecommunications and data transmission networks. These surge arresters must be installed on a symmetrical DIN rail and are available for most transmission lines: line voltage 170 V, throughput up to 10 Mbit/s. These products consist of 1 or 2 pairs with a detachable module for easy maintenance.

Classification	
UNSPSC	39121620
ETIM Class	EC000941
IGCC	4951
Commerce	
Effective date	2012-11-15
Country of origin	CN
Logistics	
GTIN/EAN	3596032712105
Customs number	8535400090
Price unit	PC
Weight of the packing unit	0.07
Length of the packing unit	0.075
Width of the packing unit	0.1
Depth of the packing unit	0.025
Norms	
Conformity to standards	IEC
Technical Characteristics	
Number of poles	1
Network type	Analogue phone line
Protection type	Low voltage
Rated voltage	170 V