

**60520050**

## Cylindrical fuse with striker gG type 14x51 400Vac 50A



### Strong points

- High-performance
- Increased reliability
- Improved safety

### General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

### Compliance with standards

- IEC 60269-1
- IEC 60269-2

### Link to the reference

<https://apac.socomec.com/en/reference/60520050>

Industrial fuses protect installations and people from overcurrents for any low voltage electrical circuit.

<b>Classification</b>	
UNSPSC	39121609
ETIM Class	EC002704
IGCC	4905
<b>Commerce</b>	
Effective date	1988-04-15
Country of origin	ES
Length of the product unit	0.038
Width of the product unit	0.0103
Weight	0.02
<b>ETIM - Electrical characteristics</b>	
Voltage type	AC
Rated current [A]	50
Rated voltage [V]	400
Rated operating frequency [Hz]	50..60
<b>ETIM - Mechanical characteristics</b>	
Size	14x51 mm
<b>ETIM - Technical features</b>	
Model	Ceramic fuse
<b>Logistics</b>	
GTIN/EAN	3596031378326
Customs number	8536105090
Price unit	PC
Weight of the packing unit	0.02
Length of the packing unit	0.0145
Width of the packing unit	0.0145
Depth of the packing unit	0.051
<b>Norms</b>	
Conformity to standards	IEC
<b>Technical Characteristics</b>	
Fuse melting indicator	with striker
Fuse size	14x51
Rated voltage	400 VAC
Rated current	50
Type	gG