

60530040

Cylindrical fuse with striker aM type 14x51 500Vac 40A



Strong points

- High-performance
- Increased reliability
- Improved safety

General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

Compliance with standards

- IEC 60269-1
- IEC 60269-2

Link to the reference

<https://apac.socomec.com/en/reference/60530040>

Industrial fuses protect installations and people from overcurrents for any low voltage electrical circuit.

Classification	
UNSPSC	39121609
ETIM Class	EC002704
IGCC	4905
Commerce	
Effective date	1988-04-15
Country of origin	ES
Length of the product unit	0.038
Width of the product unit	0.0103
Weight	0.02
ETIM - Electrical characteristics	
Voltage type	AC
Rated current [A]	40
Rated voltage [V]	500
Utilization category	aM (switchgear protection)
Rated operating frequency [Hz]	50..60
ETIM - Mechanical characteristics	
Size	14x51 mm
ETIM - Technical features	
Model	Ceramic fuse
Logistics	
GTIN/EAN	3596031378432
Customs number	8536105090
Price unit	PC
Weight of the packing unit	0.02
Length of the packing unit	0.0143
Width of the packing unit	0.0143
Depth of the packing unit	0.051
Norms	
Conformity to standards	IEC
Technical Characteristics	
Fuse melting indicator	with striker
Fuse size	14x51
Rated voltage	500 VAC
Rated current	40
Type	aM