

**57025016**

## Dead front fuse holder front operated 14x51 4P 50 A for RMS50



### Strong points

- Improved safety
- High breaking capacity
- Format and specific accessories

### General characteristics

- Improved safety.
- High breaking capacity.
- Features and options.

### Compliance with standards

- IEC 60269-2,-1
- IEC 60269-1
- IEC 60269-2
- UL E307648

### Link to the reference

<https://apac.socomec.com/en/reference/57025016>

RMS are modular fuse disconnect switches for cylindrical fuses. They provide safety disconnection and protection against overloads and short-circuits in any low voltage electrical circuit.

RMS: Fuse disconnect switches with pre-breaking auxiliary contact that signals that the fuse is present / blown.

#### ----- System -----

|                             |     |
|-----------------------------|-----|
| Fill rate E-Order Common    | 100 |
| Fill rate E-Order Selection | 75  |

#### Classification

|            |          |
|------------|----------|
| UNSPSC     | 39121624 |
| ETIM Class | EC002705 |
| IGCC       | 4974     |

#### Commerce

|                            |            |
|----------------------------|------------|
| Effective date             | 2015-01-29 |
| Country of origin          | ES         |
| Discount Policy            | 1CF50      |
| Discount Policy Label      | RM - RMS   |
| Length of the product unit | 0.11       |
| Width of the product unit  | 0.106      |
| Depth of the product unit  | 0.076      |
| Weight                     | 0.47       |

#### ETIM - Electrical characteristics

|  |     |
|--|-----|
| Nominal voltage [V]                      | 690 |
| Number of poles                          | 4   |
| Concurrently switching neutral conductor | No  |

#### ETIM - Mechanical characteristics

|                                     |          |
|-------------------------------------|----------|
| Built-in depth [mm]                 | 49.5     |
| Degree of protection (IP)           | IP2X     |
| Mounting method                     | DIN rail |
| For fuse size                       | 14x51 mm |
| Width in number of modular spacings | 4        |

#### ETIM - Technical features

|                                |     |
|--------------------------------|-----|
| Lockable                       | Yes |
| With optical defect indication | Yes |

#### Logistics

|                            |               |
|----------------------------|---------------|
| GTIN/EAN                   | 3596032843403 |
| Customs number             | 8536105090    |
| Price unit                 | PC            |
| Weight of the packing unit | 0.47          |
| Length of the packing unit | 0.12          |
| Width of the packing unit  | 0.09          |
| Depth of the packing unit  | 0.127         |

#### Norms

|                         |            |
|-------------------------|------------|
| Conformity to standards | IEC<br/>UL |
|-------------------------|------------|

#### Technical Characteristics

|                        |       |
|------------------------|-------|
| Fuse melting indicator | Yes   |
| Fuse size              | 14x51 |

|                 |           |
|-----------------|-----------|
| Number of poles | 4         |
| Rated current   | 50        |
| Size            | RM/RMS 50 |