

57030011

RM cylind. fuse holder Led sign. and W/O sign. aux. cont.-100A-1P-NFC-Fuse 22x58



Strong points

- Improved safety
- High breaking capacity
- Format and specific accessories

General characteristics

- Improved safety.
- High breaking capacity.
- Features and options.

Compliance with standards

- IEC 60269-2,-1
- IEC 60269-1
- IEC 60269-2
- UL E307648

Link to the reference

<https://apac.socomec.com/en/reference/57030011>

RMs are modular fuse disconnect switches for cylindrical fuses. They ensure safe disconnection and protection against surges and short-circuits in any low voltage electrical circuit.

Classification	
UNSPSC	39121624
ETIM Class	EC002705
IGCC	4974
Commerce	
Effective date	2012-10-09
Country of origin	ES
Length of the product unit	0.1265
Width of the product unit	0.143
Depth of the product unit	0.0765
Weight	0.16
ETIM - Electrical characteristics	
Nominal voltage [V]	690
Number of poles	1
Concurrently switching neutral conductor	Yes
ETIM - Mechanical characteristics	
Built-in depth [mm]	40
Degree of protection (IP)	IP2X
Mounting method	DIN rail
For fuse size	22x58 mm
Width in number of modular spacings	1
ETIM - Technical features	
Lockable	Yes
With optical defect indication	No
Logistics	
GTIN/EAN	3596032703790
Customs number	8536109090
Price unit	PC
Weight of the packing unit	0.16
Length of the packing unit	0.015
Width of the packing unit	0.025
Depth of the packing unit	0.027
Norms	
Conformity to standards	IEC UL
Technical Characteristics	
Fuse melting indicator	Yes
Fuse size	22x58
Number of poles	1
Rated current	100
Size	RM/RMS 100