

60630016

Cylindrical fuse with striker aM type 22x58 690Vac 16A



Industrial fuses protect installations and people from overcurrents for any low voltage electrical circuit.

Strong points

- High-performance
- Increased reliability
- Improved safety

General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

Compliance with standards

- IEC 60269-1
- IEC 60269-2

Link to the reference

<https://apac.socomec.com/en/reference/60630016>

----- System -----

Fill rate E-Order Common	83
Fill rate E-Order Selection	100

Classification

UNSPSC	39121609
ETIM Class	EC002704
IGCC	4905

Commerce

Effective date	1988-04-15
Country of origin	ES
Discount Policy	1CF10
Discount Policy Label	CYLINDRICAL FUSE
Length of the product unit	0.051
Width of the product unit	0.0143
Weight	0.05

ETIM - Electrical characteristics

Voltage type	AC
Rated current [A]	16
Rated voltage [V]	690
Utilization category	aM (switchgear protection)
Rated operating frequency [Hz]	50..60

ETIM - Mechanical characteristics

Size	14x51 mm
Type of fuse status indicator	Top fuse status indicator

ETIM - Technical features

Model	Ceramic fuse
-------	--------------

Logistics

GTIN/EAN	3596031378685
Customs number	8536105090
Price unit	PC
Weight of the packing unit	0.05
Length of the packing unit	0.022
Width of the packing unit	0.022
Depth of the packing unit	0.058

Norms

Conformity to standards	IEC
-------------------------	-----

Technical Characteristics

Fuse melting indicator	with striker
Fuse size	22x58
Rated voltage	690 VAC
Rated current	16
Type	aM