

60130002

Cylindrical fuse without striker aM type 10x38 500Vac 2A



Industrial fuses protect installations and people from overcurrents for any low voltage electrical circuit.

Strong points

- High-performance
- Increased reliability
- Improved safety

General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

Compliance with standards

- IEC 60269-1
- IEC 60269-2

Link to the reference

<https://apac.socomec.com/en/reference/60130002>

Classification

UNSPSC	39121609
ETIM Class	EC002704
IGCC	4905

Commerce

Effective date	1988-04-15
Country of origin	ES
Length of the product unit	0.038
Width of the product unit	0.0103
Weight	0.01

ETIM - Electrical characteristics

Breaking capacity [kA]	120
Power loss at rated current [W]	0.6
Voltage type	AC
Rated current [A]	2
Rated voltage [V]	500
Utilization category	aM (switchgear protection)
Rated operating frequency [Hz]	50..60

ETIM - Mechanical characteristics

Size	14x51 mm
------	----------

ETIM - Technical features

Model	Ceramic fuse
-------	--------------

Logistics

GTIN/EAN	3596031377213
Customs number	8536101090
Price unit	PC
Weight of the packing unit	0.01
Length of the packing unit	0.01
Width of the packing unit	0.01
Depth of the packing unit	0.038

Norms

Conformity to standards	IEC
-------------------------	-----

Technical Characteristics

Fuse melting indicator	without striker
Fuse size	10x38
Rated voltage	500 VAC
Rated current	2
Type	aM