

60630063

Cylindrical fuse with striker aM type 22x58 690Vac 63A



Strong points

- High-performance
- Increased reliability
- Improved safety

General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

Compliance with standards

- IEC 60269-1
- IEC 60269-2

Link to the reference

<https://apac.socomec.com/en/reference/60630063>

Industrial fuses protect installations and people from overcurrents for any low voltage electrical circuit.

Classification	
UNSPSC	39121609
ETIM Class	EC002704
IGCC	4905
Commerce	
Effective date	1988-04-15
Country of origin	ES
Length of the product unit	0.051
Width of the product unit	0.0143
Weight	0.05
ETIM - Electrical characteristics	
Voltage type	AC
Rated current [A]	63
Rated voltage [V]	690
Utilization category	aM (switchgear protection)
Rated operating frequency [Hz]	50..60
ETIM - Mechanical characteristics	
Size	14x51 mm
Type of fuse status indicator	Top fuse status indicator
ETIM - Technical features	
Model	Ceramic fuse
Logistics	
GTIN/EAN	3596031378746
Customs number	8536105090
Price unit	PC
Weight of the packing unit	0.05
Length of the packing unit	0.02
Width of the packing unit	0.02
Depth of the packing unit	0.06
Norms	
Conformity to standards	IEC
Technical Characteristics	
Fuse melting indicator	with striker
Fuse size	22x58
Rated voltage	690 VAC
Rated current	63
Type	aM