

60PV0C25

Photovoltaic cylindrical fuse gPV 30kA 14x51 1000Vdc 25A



Strong points

- High breaking capacity
- Product designed for photovoltaic systems
- Increased reliability
- Improved safety

General characteristics

- ISC MAX: short-circuit current of the string related to excess sunshine.
- IRM: maximum permissible reverse current.
- In: fuse rating or nominal fuse current (at 25°C in an RM fuse base).
- Nc: number of strings in parallel.
- UE: maximum fuse operating voltage.
- UOC MAX: maximum voltage of an open circuit in lowest temperature conditions.

Compliance with standards

- IEC 60269-6

- IEC 60269-1
- IEC 60269-2

[Link to the reference](#)
<https://apac.socomec.com/en/reference/60PV0C25>

gPV fuses protect facilities against surges related to reverse currents that can occur in photovoltaic systems.

When to protect

You must protect the PV strings from surges if the current delivered by the set minus one of the parallel strings is greater than the reverse current supported by the type of modules used in this generator.

How to protect

Protecting from overcurrents involves ensuring that both polarities are functionally grounded whether the DC is connected or not.

===== System =====

Fill rate E-Order Common	86
Fill rate E-Order Selection	100

Classification

UNSPSC	39121609
ETIM Class	EC002704
IGCC	4905

Commerce

Effective date	2011-10-19
Obsolescence date	2023-02-14
Production ban date	2023-02-14
Country of origin	ES
Discount Policy	1CF10
Discount Policy Label	CYLINDRICAL FUSE
Length of the product unit	0.0515
Width of the product unit	0.0143
Depth of the product unit	0.0101
Weight	0.02

ETIM - Electrical characteristics

Breaking capacity [kA]	30
Voltage type	DC
Rated current [A]	25
Rated voltage [V]	1000
Utilization category	gPV (photovoltaic protection)

ETIM - Mechanical characteristics

Size	14x51 mm
------	----------

ETIM - Technical features

Model	Ceramic fuse
-------	--------------

Logistics

GTIN/EAN	3596032628468
Customs number	8536105090
Price unit	PC
Weight of the packing unit	0.02
Length of the packing unit	0.051
Width of the packing unit	0.014
Depth of the packing unit	0.014

Norms

Conformity to standards	IEC
-------------------------	-----

Technical Characteristics

Fuse melting indicator	without striker
Fuse size	14x51
Rated voltage	1000 VDC
Rated current	25
Type	gPV