


63013024

Multipolar fuse base for fuses with a striker T1 3P 250A



Strong points

- High level of electrical safety
- High breaking capacity
- Fuse blown indicator
- Various mounting options

General characteristics

- High level of electrical safety.
- High breaking capacity.
- Fuse blown indicator.
- Various mounting options.

Compliance with standards

- IEC 60269-1
- IEC 60269-2
- IEC 60269-2,-1

Link to the reference

<https://apac.socomec.com/en/reference/63013024>

Fuse bases are single-pole or multi-pole solid supports for knife-edge fuses.

Classification	
UNSPSC	39121624
ETIM Class	EC000067
IGCC	4972
Commerce	
Effective date	1998-07-27
Country of origin	FR
Weight	3.13
ETIM - Electrical characteristics	
Number of poles	3
Rated current [A]	250
ETIM - Mechanical characteristics	
Construction size	NH1
ETIM - Technical features	
Bus-mounting type	No
Swivelling mechanism	No
Logistics	
GTIN/EAN	3596031379712
Customs number	8536109090
Price unit	PC
Weight of the packing unit	2.9
Length of the packing unit	0.34
Width of the packing unit	0.2
Depth of the packing unit	0.21
Norms	
Conformity to standards	IEC
Technical Characteristics	
Fuse size	NH1
Number of poles	3
Rated current	250
Type	IP2