

63014024

Multipolar fuse base for fuses with a striker T1 4P 250A



Strong points

- High level of electrical safety
- High breaking capacity
- Fuse blown indicator
- Various mounting options

General characteristics

- High level of electrical safety.
- High breaking capacity.
- Fuse blown indicator.
- Various mounting options.

Compliance with standards

- IEC 60269-1
- IEC 60269-2
- IEC 60269-2,-1

Link to the reference

Fuse bases are single-pole or multi-pole solid supports for knife-edge fuses.

Classification

UNSPSC	39121624
ETIM Class	EC000067
IGCC	4972

Commerce

Effective date	2001-12-11
Country of origin	FR
Weight	4.02

ETIM - Electrical characteristics

Number of poles	4
Rated current [A]	250

ETIM - Mechanical characteristics

Construction size	NH1
-------------------	-----

ETIM - Technical features

Bus-mounting type	No
Swivelling mechanism	No

Logistics

GTIN/EAN	3596031605774
Customs number	8536109090
Price unit	PC
Weight of the packing unit	4.02
Length of the packing unit	0.168
Width of the packing unit	0.179
Depth of the packing unit	0.264

Norms

Conformity to standards	IEC
-------------------------	-----

Technical Characteristics

Fuse size	NH1
Number of poles	4
Rated current	250
Type	IP2

<https://apac.socomec.com/en/reference/63014024>