

60320080

Cylindrical fuse without striker gG type 22x58 500Vac 80A



Strong points

- High-performance
- Increased reliability
- Improved safety

General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

Compliance with standards

- IEC 60269-1
- IEC 60269-2

Link to the reference

<https://apac.socomec.com/en/reference/60320080>

Industrial fuses protect installations and people from overcurrents for any low voltage electrical circuit.

Classification	
UNSPSC	39121609
ETIM Class	EC002704
IGCC	4905
Commerce	
Effective date	1988-04-15
Country of origin	ES
Length of the product unit	0.058
Width of the product unit	0.0222
Weight	0.054
ETIM - Electrical characteristics	
Voltage type	AC
Rated current [A]	80
Rated operating frequency [Hz]	50..60
ETIM - Mechanical characteristics	
Size	14x51 mm
ETIM - Technical features	
Model	Ceramic fuse
Logistics	
GTIN/EAN	3596031377893
Customs number	8536109090
Price unit	PC
Weight of the packing unit	0.054
Length of the packing unit	0.022
Width of the packing unit	0.022
Depth of the packing unit	0.058
Norms	
Conformity to standards	IEC
Technical Characteristics	
Fuse melting indicator	without striker
Fuse size	22x58
Rated voltage	500 VAC
Rated current	80
Type	gG