

67460800

Knife-edge fuse without striker gG type NH S4 500Vac 800A



Strong points

- High-performance
- Increased reliability
- Improved safety

General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

Compliance with standards

- IEC 60269-1
- IEC 60269-2

Link to the reference

<https://apac.socomec.com/en/reference/67460800>

Industrial fuses protect installations and people from overcurrents for any low voltage electrical circuit.

| | |
|---|-----------------|
| Classification | |
| UNSPSC | 39121612 |
| ETIM Class | EC000055 |
| IGCC | 4908 |
| Commerce | |
| Effective date | 1988-04-15 |
| Country of origin | ES |
| Length of the product unit | 0.11 |
| Width of the product unit | 0.203 |
| Depth of the product unit | 0.105 |
| Weight | 2.18 |
| ETIM - Electrical characteristics | |
| Voltage type | AC |
| Rated current [A] | 800 |
| Rated voltage AC [V] | 500 |
| ETIM - Mechanical characteristics | |
| Type of fuse status indicator | None |
| ETIM - Technical features | |
| Fuse construction type according to IEC 60269 | NH4 |
| Logistics | |
| GTIN/EAN | 3596031396016 |
| Customs number | 8536109090 |
| Price unit | PC |
| Weight of the packing unit | 2.18 |
| Length of the packing unit | 0.112 |
| Width of the packing unit | 0.134 |
| Depth of the packing unit | 0.224 |
| Norms | |
| Conformity to standards | IEC |
| Technical Characteristics | |
| Fuse melting indicator | without striker |
| Fuse size | S4 |
| Rated voltage | 500 VAC |
| Rated current | 800 |
| Type | gG |