

**60520010**

## Cylindrical fuse with striker gG type 14x51 400Vac 125A

### Strong points

- High-performance
- Increased reliability
- Improved safety

### General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

### Compliance with standards

- IEC 60269-1
- IEC 60269-2

### Link to the reference

<https://apac.socomec.com/en/reference/60520010>

Industrial fuses protect installations and people from overcurrents for any low voltage electrical circuit.

### ----- System -----

Fill rate E-Order Common	80
Fill rate E-Order Selection	100

### Classification

UNSPSC	39121609
ETIM Class	EC002704
IGCC	4905

### Commerce

Effective date	1988-04-15
Country of origin	ES
Discount Policy	1CF10
Discount Policy Label	CYLINDRICAL FUSE
Length of the product unit	0.038
Width of the product unit	0.0103
Weight	0.02

### ETIM - Electrical characteristics

Voltage type	AC
Rated current [A]	10
Rated voltage [V]	500
Rated operating frequency [Hz]	50..60

### ETIM - Mechanical characteristics

Size	14x51 mm
Type of fuse status indicator	Top fuse status indicator

### ETIM - Technical features

Model	Ceramic fuse
-------	--------------

### Logistics

GTIN/EAN	3596031378258
Customs number	8536101090
Price unit	PC
Weight of the packing unit	0.02
Length of the packing unit	0.0143
Width of the packing unit	0.0143
Depth of the packing unit	0.051

### Norms

Conformity to standards	IEC
-------------------------	-----

### Technical Characteristics

Fuse melting indicator	with striker
Fuse size	14x51
Rated voltage	400 VAC
Rated current	10
Type	gG