

**68620080**

## Knife-edge fuse with striker gG type NH S1 690Vac 80A



### Strong points

- High-performance
- Increased reliability
- Improved safety

### General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

### Compliance with standards

- IEC 60269-1
- IEC 60269-2

### Link to the reference

<https://apac.socomec.com/en/reference/68620080>

Industrial fuses protect installations and people from overcurrents for any low voltage electrical circuit.

<b>Classification</b>	
UNSPSC	39121612
ETIM Class	EC000055
IGCC	4908
<b>Commerce</b>	
Effective date	1988-04-15
Obsolescence date	2021-09-01
Production ban date	2022-02-01
Country of origin	ES
Length of the product unit	0.053
Width of the product unit	0.1375
Depth of the product unit	0.052
Weight	0.394
<b>ETIM - Electrical characteristics</b>	
Voltage type	AC
Rated current [A]	80
Rated voltage AC [V]	690
<b>ETIM - Technical features</b>	
Fuse construction type according to IEC 60269	NH1
<b>Logistics</b>	
GTIN/EAN	3596031408283
Customs number	8536109090
Price unit	PC
Weight of the packing unit	0.394
Length of the packing unit	0.14
Width of the packing unit	0.07
Depth of the packing unit	0.04
<b>Norms</b>	
Conformity to standards	IEC
<b>Technical Characteristics</b>	
Fuse melting indicator	with striker
Fuse size	S1
Rated voltage	690 VAC
Rated current	80
Type	gG