

68720125

Knife-edge fuse with striker gG type NH S2 690Vac 125A



Strong points

- High-performance
- Increased reliability
- Improved safety

General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

Compliance with standards

- IEC 60269-1
- IEC 60269-2

Link to the reference

<https://apac.socomec.com/en/reference/68720125>

Industrial fuses protect installations and people from overcurrents for any low voltage electrical circuit.

Classification

UNSPSC	39121612
ETIM Class	EC000055
IGCC	4908

Commerce

Effective date	1988-04-15
Obsolescence date	2021-09-01
Production ban date	2022-02-01
Country of origin	HU
Length of the product unit	0.061
Width of the product unit	0.1525
Depth of the product unit	0.06
Weight	0.58

ETIM - Electrical characteristics

Voltage type	AC
Rated current [A]	125
Rated voltage AC [V]	690

ETIM - Technical features

Fuse construction type according to IEC 60269	NH2
---	-----

Logistics

GTIN/EAN	3596031408481
Customs number	8536109090
Price unit	PC
Weight of the packing unit	0.58
Length of the packing unit	0.07
Width of the packing unit	0.15
Depth of the packing unit	0.055

Norms

Conformity to standards	IEC
-------------------------	-----

Technical Characteristics

Fuse melting indicator	with striker
Fuse size	S2
Rated voltage	690 VAC
Rated current	125
Type	gG