

**68720200**

## Knife-edge fuse with striker gG type NH S2 690Vac 200A



### Strong points

- High-performance
- Increased reliability
- Improved safety

### General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

### Compliance with standards

- IEC 60269-1
- IEC 60269-2

### Link to the reference

<https://apac.socomec.com/en/reference/68720200>

Industrial fuses protect installations and people from overcurrents for any low voltage electrical circuit.

<b>Classification</b>	
UNSPSC	39121612
ETIM Class	EC000055
IGCC	4908
<b>Commerce</b>	
Effective date	1988-04-15
Country of origin	HU
Length of the product unit	0.061
Width of the product unit	0.1525
Depth of the product unit	0.06
Weight	0.572
<b>ETIM - Electrical characteristics</b>	
Voltage type	AC
Rated current [A]	200
Rated voltage AC [V]	690
<b>ETIM - Technical features</b>	
Fuse construction type according to IEC 60269	NH2
<b>Logistics</b>	
GTIN/EAN	3596031408504
Customs number	8536109090
Price unit	PC
Weight of the packing unit	0.572
Length of the packing unit	0.145
Width of the packing unit	0.075
Depth of the packing unit	0.05
<b>Norms</b>	
Conformity to standards	IEC
<b>Technical Characteristics</b>	
Fuse melting indicator	with striker
Fuse size	S2
Rated voltage	690 VAC
Rated current	200
Type	gG