

**60630125**

## Cylindrical fuse with striker aM type 22x58 400Vac 125A



### Strong points

- High-performance
- Increased reliability
- Improved safety

### General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

### Compliance with standards

- IEC 60269-1
- IEC 60269-2

### Link to the reference

<https://apac.socomec.com/en/reference/60630125>

Industrial fuses protect installations and people from overcurrents for any low voltage electrical circuit.

<b>Classification</b>	
UNSPSC	39121609
ETIM Class	EC002704
IGCC	4905
<b>Commerce</b>	
Effective date	1988-04-15
Country of origin	ES
Length of the product unit	0.051
Width of the product unit	0.0143
<b>ETIM - Electrical characteristics</b>	
Voltage type	AC
Rated current [A]	125
Rated voltage [V]	690
Utilization category	aM (switchgear protection)
Rated operating frequency [Hz]	50..60
<b>ETIM - Mechanical characteristics</b>	
Size	14x51 mm
Type of fuse status indicator	Top fuse status indicator
<b>ETIM - Technical features</b>	
Model	Ceramic fuse
<b>Logistics</b>	
GTIN/EAN	3596031378777
Customs number	8536109090
Price unit	PC
Weight of the packing unit	0.54
Length of the packing unit	0.06
Width of the packing unit	0.02
Depth of the packing unit	0.02
<b>Norms</b>	
Conformity to standards	IEC
<b>Technical Characteristics</b>	
Fuse melting indicator	with striker
Fuse size	22x58
Rated voltage	400 VAC
Rated current	125
Type	aM