

## 60PV0063

### Photovoltaic knife edge fuse gPV NH1 1000VDC 63A



#### Strong points

- High breaking capacity
- Product designed for photovoltaic systems
- Increased reliability
- Improved safety

#### General characteristics

- ISC MAX: short-circuit current of the string related to excess sunshine.
- MRI: maximum permissible reverse current.
- In: fuse rating or nominal fuse current (at 25°C in an RM fuse base).
- Nc: number of strings in parallel.
- UE: maximum fuse operating voltage.
- UOC MAX: maximum voltage of an open circuit in lowest temperature conditions

#### Compliance with standards

- IEC 60269-6
- IEC 60269-1
- IEC 60269-2

#### Link to the reference

<https://apac.socomec.com/en/reference/60PV0063>

gPV fuses protect facilities against surges related to reverse currents that can occur in photovoltaic systems.

When to protect

You must protect the PV strings from surges if the current delivered by the set minus one of the parallel strings is greater than the reverse current supported by the type of modules used in this generator.

How to protect

Protecting from overcurrents involves ensuring that both polarities are functionally grounded whether the DC is connected or not.

#### ----- System -----

Fill rate E-Order Common	100
Fill rate E-Order Selection	100
<b>Classification</b>	
UNSPSC	39121612
ETIM Class	EC000055
IGCC	4908
<b>Commerce</b>	
Effective date	2011-07-13
Country of origin	IN
Discount Policy	1CF20
Discount Policy Label	FUSE WITHOUT STRIKER
Length of the product unit	0.053
Width of the product unit	0.137
Depth of the product unit	0.04
Weight	0.383
<b>ETIM - Electrical characteristics</b>	
Voltage type	DC
Rated current [A]	63
Rated voltage DC [V]	1000
Utilization category	gPV (photovoltaic protection)
<b>ETIM - Technical features</b>	
Fuse construction type according to IEC 60269	NH1
<b>Logistics</b>	
GTIN/EAN	3596032616021
Customs number	8536105090
Price unit	PC
Weight of the packing unit	0.383
Length of the packing unit	0.135
Width of the packing unit	0.04
Depth of the packing unit	0.065
<b>Norms</b>	
Conformity to standards	IEC
<b>Technical Characteristics</b>	
Fuse melting indicator	with T indicator
Fuse size	NH1
Rated voltage	1000 VDC
Rated current	63
Type	gPV