

## 87P11011

### Strong points

- High-performance power switching in a compact frame
- Safe & reliable operation
- Designed for harsh environments.
- Easy to install.
- Modular solution for flexible configuration

### General characteristics

- Range 100 A to 1200 A.
- Up to 1500 VDC.
- High-performance switching with a compact design.
- Easy integration.
- Reinforced safety with visible breaking indication.
- High efficiency with low power loss.

### Compliance with standards

- IEC 60947-3
- DC-21B & DC-PV2
- UL 98B
- CCC

### Link to the reference



<https://apac.socomec.com/en/reference/87P11011>

INOSYS LBS is a range of load break switches that are available with manual controls. They may be operated manually using the handle to disconnect all or part of an electrical installation. They allow on-load opening and closing and safe disconnection of all direct current low voltage electrical circuits up to 1500 VDC and can be used for emergency disconnection applications. They are available for the DC-PV2 use category.

<b>Classification</b>	
UNSPSC	39122233
ETIM Class	EC000216
IGCC	5290
<b>Commerce</b>	
Effective date	2018-03-01
Country of origin	FR
Discount Policy	1CD40
Discount Policy Label	INOSYS LBS PV MANUAL
<b>ETIM - Electrical characteristics</b>	
Rated permanent current Iu	100
Number of poles	2
Rated operating voltage	600..1500
Max. rated operation voltage Ue AC	1500
<b>ETIM - Mechanical characteristics</b>	
Degree of protection (IP), front side	IP20
Suitable for floor mounting	No
Suitable for front mounting 4-hole	Yes
Suitable for front mounting centre	No
Suitable for distribution board installation	Yes
Suitable for intermediate mounting	Yes
<b>ETIM - Technical features</b>	
Number of switches	1
Interlockable	Yes
Motor drive integrated	No
Type of electrical connection of main circuit	Bolt connection
Version as emergency stop installation	Yes
Type of control element	Other
Version as main switch	Yes
Version as safety switch	Yes
Version as maintenance-/service switch	Yes
Colour control element	Other
Motor drive optional	No
Voltage release optional	No
Device construction	Built-in device fixed built-in technique
Version as reversing switch	No
<b>Logistics</b>	
GTIN/EAN	3596033046735
Customs number	8535301090
Price unit	PC
Weight of the packing unit	0.01
<b>Technical Characteristics</b>	
Control operator	Direct : E2 / External : S2
Number of poles	1+1
Rated voltage	1500
Rated current	100
Type	Frontal or lateral operation
Frame size	F2