


**65011132**

## Fuse base for fuses without a striker T2 3P 400A DIN rail-mounted device



### Strong points

- High level of electrical safety
- High breaking capacity
- Fuse blown indicator
- Various mounting options

### General characteristics

- High level of electrical safety.
- High breaking capacity.
- Fuse blown indicator.
- Various mounting options.

### Compliance with standards

- IEC 60269-1
- IEC 60269-2
- IEC 60269-2,-1

### Link to the reference

<https://apac.socomec.com/en/reference/65011132>

Fuse bases are single-pole or multi-pole solid supports for knife-edge fuses.

<b>Classification</b>	
UNSPSC	39121624
ETIM Class	EC000067
IGCC	4972
<b>Commerce</b>	
Effective date	2003-01-09
Country of origin	ES
Weight	1.79
<b>ETIM - Electrical characteristics</b>	
Number of poles	3
Rated current [A]	400
<b>ETIM - Mechanical characteristics</b>	
Construction size	NH2
<b>ETIM - Technical features</b>	
Bus-mounting type	No
Swivelling mechanism	No
<b>Logistics</b>	
GTIN/EAN	3596031652419
Customs number	8536109090
Price unit	PC
Weight of the packing unit	1.79
Length of the packing unit	0.2
Width of the packing unit	0.105
Depth of the packing unit	0.273
<b>Norms</b>	
Conformity to standards	IEC
<b>Technical Characteristics</b>	
Fuse size	NH2
Number of poles	3
Rated current	400
Type	DIN rail mounting