

87P22061

Strong points

- High-performance power switching in a compact frame
- Safe & reliable operation
- Designed for harsh environments.
- Easy to install.
- Modular solution for flexible configuration

General characteristics

- Range 100 A to 1200 A.
- Up to 1500 VDC.
- High-performance switching with a compact design.
- Easy integration.
- Reinforced safety with visible breaking indication.
- High efficiency with low power loss.

Compliance with standards

- IEC 60947-3
- DC-21B & DC-PV2
- UL 98B
- CCC

Link to the reference

<https://apac.socomec.com/en/reference/87P22061>

INOSYS LBS is a range of load break switches that are available with manual controls. They may be operated manually using the handle to disconnect all or part of an electrical installation. They allow on-load opening and closing and safe disconnection of all direct current low voltage electrical circuits up to 1500 VDC and can be used for emergency disconnection applications. They are available for the DC-PV2 use category.

Commerce

Effective date	2021-04-29
Country of origin	TN

Logistics

GTIN/EAN	3596033173196
Customs number	8535301090