


95064012

## Remotely operated transfer switch ATyS S 4P 125A 24/48 VDC



### Strong points

- Extensive power supply range
- Safety and reliability
- Easy integration
- Simplified maintenance

### General characteristics

- Range from 40A to 125A.
- Available in 4P.
- Compact design.

### Compliance with standards

- IEC 60947-6-1
- IEC 60947-3
- GB/T 14048.11

### Link to the reference

<https://apac.socomec.com/en/reference/95064012>

ATyS S products are 4 pole remotely operated transfer switches with positive break indication.

They enable the on-load transfer of two three-phase supplies via remote volt-free contacts, from either an external automatic controller, using pulse logic, or a switch. They are intended for use in low voltage power supply systems where a brief interruption of the load supply is acceptable during transfer.

### ----- System -----

Fill rate E-Order Common	86
Fill rate E-Order Selection	73

### Classification

UNSPSC	39122205
ETIM Class	EC000216
IGCC	5177

### Commerce

Effective date	2013-01-21
Country of origin	IN
Discount Policy	1CB65
Discount Policy Label	ATYS S
Length of the product unit	0.1435
Width of the product unit	0.198
Depth of the product unit	0.181
Weight	3.25

### ETIM - Electrical characteristics

Max. rated operation voltage Ue AC [V]	800
Rated operating voltage [V]	400..415
Rated permanent current Iu [A]	125
Rated permanent current at AC-23, 400 V [A]	63
Rated permanent current at AC-21, 400 V [A]	125
Rated short-time withstand current Icw [kA]	2.5
Conditioned rated short-circuit current Iq [kA]	15
Number of poles	4

### ETIM - Mechanical characteristics

Suitable for floor mounting	No
Suitable for front mounting 4-hole	No
Suitable for front mounting centre	No
Suitable for distribution board installation	Yes
Suitable for intermediate mounting	Yes
Colour control element	Other
Degree of protection (IP), front side	IP20

### ETIM - Technical features

Version as main switch	Yes
Version as maintenance-/service switch	Yes
Version as safety switch	Yes
Version as emergency stop installation	No
Version as reversing switch	Yes
Number of switches	2
Number of auxiliary contacts as normally open contact	3

Motor drive optional	No
Motor drive integrated	Yes
Voltage release optional	No
Device construction	Built-in device fixed built-in technique
Type of control element	Other
Interlockable	Yes
Type of electrical connection of main circuit	Bolt connection

#### Logistics

GTIN/EAN	3596032730123
Customs number	8536508090
Price unit	PC
Weight of the packing unit	3.25
Length of the packing unit	0.212
Width of the packing unit	0.173
Depth of the packing unit	0.237

#### Norms

Conformity to standards	CCC IEC
-------------------------	-------------

#### Technical Characteristics

Control operator	RTSE
Number of poles	4
Rated current	125
Type	RTSE
Frame size	ATYS S