

**68720400**

## Knife-edge fuse with striker gG type NH S2 500Vac 400A



### Strong points

- High-performance
- Increased reliability
- Improved safety

### General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

### Compliance with standards

- IEC 60269-1
- IEC 60269-2

### Link to the reference

<https://apac.socomec.com/en/reference/68720400>

Industrial fuses protect installations and people from overcurrents for any low voltage electrical circuit.

#### ===== System =====

Fill rate E-Order Common	100
Fill rate E-Order Selection	100

#### Classification

UNSPSC	39121612
ETIM Class	EC000055
IGCC	4908

#### Commerce

Effective date	1988-04-15
Country of origin	HU
Discount Policy	1CF30
Discount Policy Label	FUSE WITH STRIKER
Length of the product unit	0.061
Width of the product unit	0.1525
Depth of the product unit	0.06
Weight	0.578

#### ETIM - Electrical characteristics

Voltage type	AC
Rated current [A]	400
Rated voltage AC [V]	500

#### ETIM - Technical features

Fuse construction type according to IEC 60269	NH2
---	-----

#### Logistics

GTIN/EAN	3596031408542
Customs number	8536109090
Price unit	PC
Weight of the packing unit	0.578
Length of the packing unit	0.07
Width of the packing unit	0.055
Depth of the packing unit	0.16

#### Norms

Conformity to standards	IEC
-------------------------	-----

#### Technical Characteristics

Fuse melting indicator	with striker
Fuse size	S2
Rated voltage	500 VAC
Rated current	400
Type	gG