


**87P02010**

## DC LOAD BREAK SWITCH INOSYS LBS MANUEL UL 100A 2P 1000VDC F2



### Strong points

- High-performance power switching in a compact frame
- Safe & reliable operation
- Designed for harsh environments.
- Easy to install.
- Modular solution for flexible configuration

### General characteristics

- Range 100 A to 1200 A.
- Up to 1500 VDC.
- High-performance switching with a compact design.
- Easy integration.
- Reinforced safety with visible breaking indication.
- High efficiency with low power loss.

### Compliance with standards

- IEC 60947-3
- DC-21B & DC-PV2
- UL 98B
- CCC

### Link to the reference

<https://apac.socomec.com/en/reference/87P02010>

INOSYS LBS is a range of load break switches that are available with manual controls. They may be operated manually using the handle to disconnect all or part of an electrical installation. They allow on-load opening and closing and safe disconnection of all direct current low voltage electrical circuits up to 1500 VDC and can be used for emergency disconnection applications. They are available for the DC-PV2 use category.

----- System -----	
Fill rate E-Order Common	86
Fill rate E-Order Selection	78
Classification	
UNSPSC	39122233
ETIM Class	EC000216
IGCC	5290
Commerce	
Effective date	2015-10-02
Country of origin	TN
Discount Policy	1CD40
Discount Policy Label	INOSYS LBS PV MANUAL
Length of the product unit	0.154
Width of the product unit	0.117
Depth of the product unit	0.11
Weight	0.01
ETIM - Electrical characteristics	
Max. rated operation voltage Ue AC [V]	1000
Rated operating voltage [V]	600..1000
Rated permanent current Iu [A]	100
Rated short-time withstand current Icw [kA]	5
Number of poles	2
ETIM - Mechanical characteristics	
Suitable for floor mounting	No
Suitable for front mounting 4-hole	Yes
Suitable for front mounting centre	No
Suitable for distribution board installation	Yes
Suitable for intermediate mounting	Yes
Colour control element	Other
Degree of protection (IP), front side	IP20
ETIM - Technical features	
Version as main switch	Yes
Version as maintenance-/service switch	Yes
Version as safety switch	Yes
Version as emergency stop installation	Yes
Version as reversing switch	No
Number of switches	1
Motor drive optional	No
Motor drive integrated	No
Voltage release optional	No
Device construction	Built-in device fixed built-in technique
Type of control element	Other

Interlockable	Yes
Type of electrical connection of main circuit	Bolt connection
<b>Logistics</b>	
GTIN/EAN	3596032977689
Customs number	8536508090
Price unit	PC
Weight of the packing unit	0.01
Length of the packing unit	0.2045
Width of the packing unit	0.17
Depth of the packing unit	0.39
<b>Norms</b>	
Conformity to standards	IEC UL
<b>Technical Characteristics</b>	
Control operator	Direct : E2 / External : S2
Number of poles	2
Rated voltage	1000
Rated current	100
Type	Frontal or lateral operation
Frame size	F2