

95733100

Automatic transfer switch ATyS p 3P 1000A



Strong points

- Recording of events
- Optional communication modules
- Configuration software
- Power measurements
- Possibility to set periodic genset startup
- More robust
- Security and reliability

General characteristics

- Range from 125A to 3200A.
- Available in 3P or 4P.
- Recording of events.
- Robust design
- Safety and reliability.

Compliance with standards

- IEC 60947-6-1
- IEC 60947-3
- GB/T 14048.11

Link to the reference

<https://apac.socomec.com/en/reference/95733100>

ATyS p are 3 or 4 pole automatic transfer switches with positive break indication. They incorporate all the functions offered by the ATyS t and g, as well as functions designed for power management and functions communication. In automatic mode they enable the monitoring of, and the on-load changeover between, two power supply sources, in accordance with the parameters configured through LCD display, or via communication. They are intended for use in low voltage power supply systems where a brief interruption of the load supply is acceptable during transfer.

----- System -----

Fill rate E-Order Common	86
Fill rate E-Order Selection	100

Classification

UNSPSC	39122205
ETIM Class	EC000216
IGCC	5177

Commerce

Effective date	2012-06-21
Country of origin	FR
Discount Policy	1CB79
Discount Policy Label	ATYS P
Length of the product unit	0.321
Width of the product unit	0.504
Depth of the product unit	0.3915
Weight	45

ETIM - Electrical characteristics

Max. rated operation voltage Ue AC [V]	1000
Rated operating voltage [V]	400..690
Rated permanent current Iu [A]	1000
Rated permanent current at AC-23, 400 V [A]	1000
Rated permanent current at AC-21, 400 V [A]	1000
Rated short-time withstand current Icw [kA]	35
Rated operation power at AC-23, 400 V [kW]	600
Switching power at 400 V [kW]	8000
Conditioned rated short-circuit current Iq [kA]	50
Number of poles	3

ETIM - Mechanical characteristics

Suitable for floor mounting	No
Suitable for front mounting 4-hole	No
Suitable for front mounting centre	No
Suitable for distribution board installation	No
Suitable for intermediate mounting	Yes
Colour control element	Other
Degree of protection (IP), front side	IP20

ETIM - Technical features

Version as main switch	Yes
Version as maintenance-/service switch	Yes
Version as safety switch	Yes
Version as emergency stop installation	No

Version as reversing switch	Yes
Number of switches	2
Number of auxiliary contacts as normally open contact	3
Motor drive optional	No
Motor drive integrated	Yes
Voltage release optional	No
Device construction	Built-in device fixed built-in technique
Type of control element	Other
Interlockable	Yes
Type of electrical connection of main circuit	Bolt connection

Logistics

GTIN/EAN	3596032776015
Customs number	8536508090
Price unit	PC
Weight of the packing unit	45
Length of the packing unit	0.8
Width of the packing unit	0.6
Depth of the packing unit	0.73

Norms

Conformity to standards	CCC IEC
-------------------------	-------------

Technical Characteristics

Control operator	Automatic fully programmable
Number of poles	3
Rated current	1000
Type	Class PC
Frame size	B6