

93444004

Automatic transfer switch ATyS t M 4P 40A 230/400 VAC



Strong points

- Quick start
- Dedicated to three-phase mains/mains applications
- Secure programming
- Secure
- High-speed transfer
- Superior electrical performance
- Immune to voltage fluctuations

General characteristics

- For main/main application.
- Range from 40A to 160A.
- Available in 4P.
- Easy selection of AUT/MAN mode.
- Manual emergency operation.
- Padlocking facility.

Compliance with standards

- IEC 60947-6-1
- IEC 60947-3
- GB 14048.11

Link to the reference

<https://apac.socomec.com/en/reference/93444004>

ATyS t M are modular automatic transfer switches with positive break indication. They are 4 pole (three-phase) devices. They have all the functions of the ATyS d M together with an integrated controller, giving them automatic features dedicated to mains/mains applications. They are intended for use in low voltage power supply systems where a brief interruption of the load supply is acceptable during transfer.

Classification

UNSPSC	39122205
ETIM Class	EC000216
IGCC	5177

Commerce

Effective date	2014-02-14
Country of origin	TN
Length of the product unit	0.245
Width of the product unit	0.34
Depth of the product unit	0.0735
Weight	4.3

ETIM - Electrical characteristics

Max. rated operation voltage Ue AC [V]	800
Rated operating voltage [V]	400..690
Rated permanent current Iu [A]	40
Rated permanent current at AC-23, 400 V [A]	40
Rated permanent current at AC-21, 400 V [A]	40
Rated short-time withstand current Icw [kA]	4
Rated operation power at AC-23, 400 V [kW]	18.5
Switching power at 400 V [kW]	18.5
Conditioned rated short-circuit current Iq [kA]	50
Number of poles	4

ETIM - Mechanical characteristics

Suitable for floor mounting	No
Suitable for front mounting 4-hole	No
Suitable for front mounting centre	No
Suitable for distribution board installation	Yes
Suitable for intermediate mounting	Yes
Colour control element	Other
Degree of protection (IP), front side	IP20

ETIM - Technical features

Version as main switch	Yes
Version as maintenance-/service switch	Yes
Version as safety switch	Yes
Version as emergency stop installation	No
Version as reversing switch	Yes
Number of switches	2
Motor drive optional	No
Motor drive integrated	Yes
Voltage release optional	No
Device construction	Built-in device fixed built-in technique
Type of control element	Other

Interlockable	Yes
Type of electrical connection of main circuit	Screw connection
Logistics	
GTIN/EAN	3596032819415
Customs number	8536508090
Price unit	PC
Weight of the packing unit	4.3
Length of the packing unit	0.395
Width of the packing unit	0.12
Depth of the packing unit	0.31
Norms	
Conformity to standards	CCC IEC
Technical Characteristics	
Control operator	Automatic programmable
Number of poles	4
Rated current	40
Type	ATSE
Frame size	ATYS M