


93532010

Automatic transfer switch ATyS g M 2P 100A 230 VAC



Strong points

- Quick start
- Dedicated to mains/genset applications
- Secure programming
- Secure
- High-speed transfer
- Superior electrical performance
- Immune to voltage fluctuations

General characteristics

- For mains/genset applications.
- Range from 40A to 160A.
- Available in 2P or 4P.
- Easy selection of AUT/MAN mode.
- Manual emergency operation.
- Padlocking facility.

Compliance with standards

- IEC 60947-6-1
- IEC 60947-3
- GB 14048.11

Link to the reference

<https://apac.socomec.com/en/reference/93532010>

ATyS g M are modular automatic transfer switches with positive break indication. They are 2 or 4 pole (single or three-phase) devices. They have all the functions of the ATyS d M together with an integrated controller, giving them automatic features dedicated and mains/genset applications. They are intended for use in low voltage power supply systems where a brief interruption of the load supply is acceptable during transfer.

----- System -----	
Fill rate E-Order Common	86
Fill rate E-Order Selection	100
Classification	
UNSPSC	39122205
ETIM Class	EC000216
IGCC	5177
Commerce	
Effective date	2014-02-14
Country of origin	TN
Discount Policy	1CB75
Discount Policy Label	ATYS T & G M
Length of the product unit	0.245
Width of the product unit	0.235
Depth of the product unit	0.0735
Weight	3.556
ETIM - Electrical characteristics	
Max. rated operation voltage Ue AC [V]	800
Rated operating voltage [V]	400..690
Rated permanent current Iu [A]	100
Rated permanent current at AC-23, 400 V [A]	100
Rated permanent current at AC-21, 400 V [A]	100
Rated short-time withstand current Icw [kA]	4
Rated operation power at AC-23, 400 V [kW]	51
Switching power at 400 V [kW]	51
Conditioned rated short-circuit current Iq [kA]	50
Number of poles	2
ETIM - Mechanical characteristics	
Suitable for floor mounting	No
Suitable for front mounting 4-hole	No
Suitable for front mounting centre	No
Suitable for distribution board installation	Yes
Suitable for intermediate mounting	Yes
Colour control element	Other
Degree of protection (IP), front side	IP20
ETIM - Technical features	
Version as main switch	Yes
Version as maintenance-/service switch	Yes
Version as safety switch	Yes
Version as emergency stop installation	No
Version as reversing switch	Yes
Number of switches	2

Motor drive optional	No
Motor drive integrated	Yes
Voltage release optional	No
Device construction	Built-in device fixed built-in technique
Type of control element	Other
Interlockable	Yes
Type of electrical connection of main circuit	Screw connection

Logistics

GTIN/EAN	3596032819507
Customs number	8536508090
Price unit	PC
Weight of the packing unit	3.556
Length of the packing unit	0.4
Width of the packing unit	0.3
Depth of the packing unit	0.115

Norms

Conformity to standards	CCC IEC
-------------------------	-------------

Technical Characteristics

Control operator	Automatic programmable for GENSET
Number of poles	2
Rated current	100
Type	ATSE
Frame size	ATYS M