

NPE-B600

NETYS PE 600VA BASIS



Strong points

- Ideal and cost-effective protection for SOHO or POS applications
- Easy to use
- A solution for network power cuts and voltage fluctuations
- Simplified connection
- Protection for your data line

General characteristics

- Minitower case.
- Step Wave, AVR function (Automatic Voltage Regulation).
- Control panel with LCD display.
- LOCAL VIEW software for local UPS monitoring.
- NTP data line suppressor.
- Up to 6 UPS output sockets.

Compliance with standards

- IEC/EN 62040-1, IEC/EN 62040-2
- AS 62040.1.1, AS 62040.1.2, AS 62040.2
- CE
- RCM (E2376)

Link to the reference

<https://apac.socomec.com/en/reference/NPE-B600>

Protection for small office, personal or point-of-sale applications.

Classification	
UNSPSC	39121011
ETIM Class	EC000382
IGCC	4149
Commerce	
Description (240 char.)	NeTYS PE 600VA/360W 230V 50/60Hz BATTERY INCLUDED WITH AVR, STEPWAVE BASIS VERSION
Effective date	2012-09-01
Country of origin	CN
Discount Policy	D02
Discount Policy Label	NETYS PE
Length of the product unit	0.145
Width of the product unit	0.1
Depth of the product unit	0.3
Weight	5
ETIM - Electrical characteristics	
Input voltage [V]	140..300
Primary frequency [Hz]	45..66
Number of phases primary	1
Output voltage [V]	230..230
Secondary frequency [Hz]	50..60
Output effective power [W]	360
Output apparent power [VA]	600
Number of phases secondary	1
SNMP	No
Voltage type	AC
Output power factor	0.6
ETIM - Mechanical characteristics	
Height [mm]	145
Width [mm]	100
Depth [mm]	300
Weight [kg]	5
Construction type	Free standing model
Input connection	C14
Number of output connections C13	4
ETIM - Technical features	
USB interface	No
Bridging time full load [min]	2
Suitable for network-management	No
USV- technology	Line-interactive
Overall efficiency [%]	98
Efficiency in eco-mode [%]	98
Potential free switch contact	No
Auto shut down function	No
Logistics	
GTIN/EAN	8027122515146

Customs number	8504409590
Weight of the packing unit	5
Length of the packing unit	0.3
Width of the packing unit	0.1
Depth of the packing unit	0.145
Norms	
Conformity to standards	IEC
Technical Characteristics	
Depth	300
Height	145
In/out	1/1
Output voltage	230
Rated frequency	50/50
Width	100
Sn	0.6
Pn	0.36
Conf	M2
Input voltage	230
Rate (min)	0.6
Rate (max)	0.6
Life Time	03-05
Configuration	Line-Interactive UPS with AVR