

## NPR-1000-MT

# NETYS PR MT 1000VA USB LCD



### Strong points

- Professional line interactive UPS
- A solution for network power cuts and voltage fluctuations
- Easy to use
- Simplified connection
- Protection for your data line

### General characteristics

- Minitower case to easily fit close to the IT load.
- Sine Wave, AVR function (Automatic Voltage Regulation).
- Control panel with LCD display.
- LOCAL VIEW software for local UPS monitoring.
- NTP data line suppressor.
- Up to 6 UPS output sockets.

### Compliance with standards

- IEC/EN 62040-1, IEC/EN 62040-2
- AS 62040.1.1, AS 62040.1.2, AS 62040.2
- CE
- RCM (E2376)

### Link to the reference

<https://apac.socomec.com/en/reference/NPR-1000-MT>

The NETYS PR is the ideal solution for protecting small servers and high performance CAD or graphic workstations

Classification	
UNSPSC	39121011
ETIM Class	EC000382
IGCC	4149
Commerce	
Description (240 char.)	NeTYS PR-MT 1000VA/700W 230V 50/60Hz WITH AVR, SINEWAVE,LCD PLUGS PROTECTED RJ45,USB BATTERY INCLUDED
Effective date	2012-09-01
Country of origin	CN
Discount Policy	D03
Discount Policy Label	NETYS PR
Length of the product unit	0.165
Width of the product unit	0.145
Depth of the product unit	0.345
Weight	9.2
ETIM - Electrical characteristics	
Input voltage [V]	170..280
Primary frequency [Hz]	45..66
Number of phases primary	1
Output voltage [V]	230..230
Secondary frequency [Hz]	50..60
Output effective power [W]	700
Output apparent power [VA]	1000
Number of phases secondary	1
SNMP	Yes
Voltage type	AC
Output power factor	0.7
ETIM - Mechanical characteristics	
Height [mm]	165
Width [mm]	145
Depth [mm]	345
Weight [kg]	9.2
Construction type	Free standing model
Input connection	C14
Number of output connections C13	4
ETIM - Technical features	
USB interface	Yes
Bridging time full load [min]	7.6
Suitable for network-management	Yes
USV- technology	Line-interactive
Overall efficiency [%]	98
Efficiency in eco-mode [%]	98
Potential free switch contact	Yes
Auto shut down function	Yes

### Logistics

GTIN/EAN	8027122515245
Customs number	8504409590
Weight of the packing unit	9.2
Length of the packing unit	0.345
Width of the packing unit	0.145
Depth of the packing unit	0.165

### Norms

Conformity to standards	IEC
-------------------------	-----

### Technical Characteristics

Depth	345
Height	165
In/out	1/1
Output voltage	230
Rated frequency	50/50
Width	145
Sn	1
Pn	0.7
Conf	M2
Input voltage	230
Rate (min)	1
Rate (max)	1
Life Time	03-05
Typical Backup Time	4
Configuration	Line-Interactive UPS with AVR